

Garant
GARANT Master eco VDI toolholder, form C4 axial, left-hand, Shank \varnothing d1: 20mm

Order data

Order number	319136 20
GTIN	4067263238089
Item class	31V

Description
Version:

- Case-hardened HRC 58 \pm 2.
- All functional faces ground.
- With ball spray nozzles.

GARANT eco – For use with normal clamping toolholders, with GARANT eco – system grooving toolholders No. 273830 – 273891 and with GARANT eco – parting-off toolholders No. 273651.

Application:

For face cutting in.

Standard:

ISO 10889 / DIN 69880 / VDI 3425, Blatt 2.

Technical description

Shank \varnothing D ₁	20 mm
h ₂	22 mm
Shank width b ₃	13 mm
Colour code for VDI shanks	VDI 20

h_6	30 mm
b_1	52 mm
b_2	27 mm
h_1	16 mm
l_1	55 mm
h_5	25 mm
Shape	C
Type of product	VDI tool arbor