

**Garant**
**GARANT Master eco VDI toolholder, form C4 axial, left-hand, Shank  $\varnothing$  d1: 25mm**

**Order data**

Order number	319136 25
GTIN	4067263238096
Item class	31V

**Description**
**Version:**

- Case-hardened HRC 58  $\pm$  2.
- All functional faces ground.
- With ball spray nozzles.

**GARANT eco – For use with normal clamping toolholders, with GARANT eco – system grooving toolholders No. 273830 – 273891 and with GARANT eco – parting-off toolholders No. 273651.**

**Application:**

For face cutting in.

**Standard:**

ISO 10889 / DIN 69880 / VDI 3425, Blatt 2.

**Technical description**

b <sub>1</sub>	58 mm
h <sub>5</sub>	25 mm
Colour code for VDI shanks	VDI 25
b <sub>2</sub>	33 mm

$h_1$	16 mm
Shank $\varnothing D_1$	25 mm
Shank width $b_3$	19 mm
$h_6$	30 mm
$l_1$	55 mm
Shape	C
Type of product	VDI tool arbor