



Digital dial thickness gauge, Measuring range: 0-12,5mm



Order data

Order number	438191 0-12,5
GTIN	4031452200546
Item class	46C

Description

Version:

Digital dial thickness gauge with lift-off lever (gauging force is independent of the user), lightweight frame, painted. Measuring faces hardened and ground.

Data transmission via RS 232 or USB with data transmission cable (not included in the scope of supply).

Supplied with:

1 battery No. 081560 size CR2032.

Technical description

Power supply	Battery-powered
Article no of the battery / rechargeable battery fitted	081560 CR2032
Throat	50 mm
Number of batteries contained	1
Battery type	Button cell
Measuring face Ø	10 mm

Measuring range	0 - 12.5 mm
Scale divisions	0.001 mm
Interface	USB interface
Interface	Digimatic interface
Packaging	sturdy box
Measurement variation E MPE (measurement range)	0.004 mm
Standard	Works standard
Type of measurement face	hardened and ground
Measurement technology	digital
Calibration	C6
Type of product	Quick thickness gauge

Services

CalibrationDial thickness gauge maximum measuring range 200	023420 200
DAkkS calibrationDial thickness gauge maximum measuring range 30	023430 30

Accessories

Button cell / special battery Battery type CR2032	081560 CR2032
---	---------------