

HEDI

All-plastic cable drum, Type: 20N2



Order data

| | |
|--------------|---------------|
| Order number | 081131 20N2 |
| GTIN | 4003644024858 |
| Item class | 08B |

Description

Version:

HEDI® cable reels stand for “Made in Germany” quality and a long service life. The drum body is specially designed to optimally guide the cable. The integrated rotation stop switch prevents accidental rotation of the drum. All cable drums are equipped with thermal cut-out switches. Sturdy cable drum of high-impact plastic with **thermal overload protection. Certified for continuous exterior use and for use in humid environments.**

- **400 V CEE input plug 16 A.**
- **1 pc. 400 V CEE output plug 16 A with self-closing cover and thermal cut-out switch.**
- **2 pcs. 250 V standard Schuko sockets with self-closing covers.**
- **Inclined 7 degrees for greater ground clearance and to make it comfortable to carry.**
- **Removable cable holder and guide for optimum cable control.**
- **Water drainage grooves.**
- **Easy to mount on a wall.**

Compact, high-quality HEDI® all-plastic cable reel with a reel diameter of 250 mm and ergonomic and safety features.

Function:

IP44: Protected against splashed water from all directions and protected against penetration by foreign bodies with $\varnothing > 1$ mm, however tools and wires should be kept away.

Technical description

| | |
|-----------------------------------|------------------------|
| IP Index of Protection | IP 44 |
| Cable class | H07RN-F |
| Cable length | 20 m |
| impact-resistant and splash-proof | Category 2 (K2) to BGI |
| Material cable | Neoprene rubber |
| Rated power unrolled | 5500 (16 A) W |
| Cable structure | 5G2.5 |
| Nominal voltage | 400 V |
| Power supply | Mains-powered |
| Type of product | Cable drum |