

HEDI

All-plastic cable drum for F, B, PL and CZ, Type: 20N2



Order data

Order number	081132 20N2
GTIN	4003644024865
Item class	08B

Description

Version:

HEDI® cable reels stand for “Made in Germany” quality and a long service life. The drum body is specially designed to optimally guide the cable. The integrated rotation stop switch prevents accidental rotation of the drum. All cable drums are equipped with thermal cut-out switches. Sturdy cable drum of high-impact plastic with **thermal overload protection. Certified for continuous exterior use and for use in humid environments.**

- **400 V CEE input plug 16 A.**
- **1 pc. 400 V CEE output plug 16 A with self-closing cover and thermal cut-out switch.**
- **2 pcs. 250 V standard Schuko sockets with self-closing covers.**
- **Inclined 7 degrees for greater ground clearance and to make it comfortable to carry.**
- **Removable cable holder and guide for optimum cable control.**
- **Water drainage grooves.**
- **Easy to mount on a wall.**

Compact, high-quality HEDI® all-plastic cable reel with a reel diameter of 250 mm and ergonomic and safety features.

With sockets for **France, Belgium, Poland and the Czech Republic.**

Function:

IP44: Protected against splashed water from all directions and protected against penetration by foreign bodies with $\varnothing > 1$ mm, however tools and wires should be kept away.

Technical description

Power supply	Mains-powered
Material cable	Neoprene rubber
IP Index of Protection	IP 44
Rated power unrolled	5500 (16 A) W
Cable class	H07RN-F
Cable length	20 m
Nominal voltage	400 V
impact-resistant and splash-proof	Category 2 (K2) to BGI
Cable structure	5G2.5
Type of product	Cable drum