



## Cordless hammer drill / driver, Type: M18FPD3-2



### Order data

Order number	070110 M18FPD3-2
GTIN	
Item class	03L

### Description

#### Version:

- Powerful cordless 2-speed hammer drill /screwdriver with multi-stage torque setting.
- REDLITHIUM-ION™ Red Li-ion batteries with single-cell monitoring and charge display.
- Sturdy metal gearbox for long working life.
- FIXTEC metal quick-change chuck with spindle lock.
- Handle with Softgrip coating for comfortable use.
- LED illumination of the working area.
- Brushless POWERSTATE™-motor (not size M18BPD4) for very high efficiency. Very low wear and up to 10 times the working life of standard DC motors.
- REDLINK PLUS™ electronics overload protection and power management.

Cordless hammer drill / driver with high torque of 158 Nm and a total length of only 175 mm.

#### Note:

See No. 073814 – 073816, 073827 and 073840 for suitable batteries and chargers.

The suitable Bluetooth tracking module can be found under 070103 BTT-1.

### Technical description

maximum twist drill size Ø in concrete	16 mm
--	-------

maximum twist drill size Ø in wood	89 mm
maximum speed 2nd speed	2100 min <sup>-1</sup>
maximum vibration to EN without hammer drill function	1.85 m/s <sup>2</sup>
Packaging	Modular case (HD=Heavy Duty)
Motor design	FUEL™
Type of rechargeable battery	Lithium-ion
Manufacturer's designation	M18 FPD3
maximum torque	158 Nm
typical application	Heavy Duty
Quick-clamping chuck range	1.5 - 13 mm
suitable battery - supplier / battery type / voltage	Milwaukee type B 18 V
maximum speed 1st speed	0 - 500 min <sup>-1</sup>
Battery voltage	18 V
Power supply	Mains operated
maximum vibration to EN with hammer drill function	11.3 m/s <sup>2</sup>
Weight	2.1 kg
Battery capacity	2 Ah
Number of rechargeable batteries contained	2
maximum twist drill size Ø in steel	16 mm
Type of product	limpact drill /screwdriver

## Accessories

Li-ion system M18B5 Battery type MB18	073816 MB18
---------------------------------------	-------------