

AEG

Cordless compact combi drill, Type: BSB18SBL2



Order data

Order number	070115 BSB18SBL2
GTIN	4058546403423
Item class	07A

Description

Version:

2-Speed cordless impact drill screwdriver with brushless motor.

- **Electronic speed control for smooth, safe starts to drilling and screw driving; reversible.**
- **2-speed all-metal gearbox with selectable hammer drive in metal, stone and masonry.**
- **Multi-stage torque adjustment and removable drill chuck.**

Handy and powerful 18 V "Sub-Compact" cordless impact wrench.

Supplied with:

Without battery and without charger, in a cardboard box.

Note:

Suitable batteries can be found under No. 073846 – 073848, suitable chargers and starter sets can be found under No. 073841 and 073844.

Technical description

maximum speed 1st speed	0 - 500 min ⁻¹
Type of rechargeable battery	Lithium-ion
maximum twist drill size Ø in concrete	13 mm

Weight	1.7 kg
Power supply	Mains operated
Number of rechargeable batteries contained	0
maximum torque hard	65 Nm
Manufacturer's designation	BSB18SBL2-0
typical application	Heavy Duty
suitable battery - supplier / battery type / voltage	AEG type AS 18 V
maximum torque soft	32 Nm
Battery voltage	18 V
Motor design	Brushless
maximum speed 2nd speed	1700 min ⁻¹
maximum vibration to EN without hammer drill function	< 2,5 m/s ²
maximum twist drill size Ø in steel	13 mm
Packaging	Modular case (HD=Heavy Duty)
Quick-clamping chuck range	1.5 - 13 mm
maximum twist drill size Ø in wood	40 mm