

AEG

Cordless compact combi drill, Type: BSB18C2X22



Order data

Order number	070229 BSB18C2X22
GTIN	4058546010850
Item class	07A

Description

Version:

2-Speed cordless combi drill with brushless motor.

- **Electronic speed control for smooth, safe starts to drilling and screw driving; reversible.**
- **2-speed all-metal gearbox with selectable hammer drive in metal, stone and masonry.**
- **Multi-stage torque adjustment and removable drill chuck.**

Compact and powerful 18V cordless impact wrench for the most demanding applications. Drill chuck is removable.

Supplied with:

Supplied with 2x 18 V / 2.0 Ah PRO Li-ion batteries, charger, transport case.

Note:

Suitable batteries can be found under No. 073846 – 073848, suitable chargers and starter sets can be found under No. 073841 and 073844.

Technical description

maximum twist drill size Ø in wood	45 mm
Power supply	Mains operated

maximum twist drill size Ø in concrete	14 mm
suitable battery - supplier / battery type / voltage	AEG type AS 18 V
Quick-clamping chuck range	1.5 - 13 mm
Motor design	Brushless
maximum vibration to EN without hammer drill function	< 2,5 m/s ²
maximum speed 2nd speed	1800 min ⁻¹
Packaging	Carrying case
Manufacturer's designation	BSB18C2XLI-202C
Number of rechargeable batteries contained	2
Battery capacity	2 Ah
Weight	1.7 kg
typical application	Heavy Duty
maximum torque soft	32 Nm
maximum speed 1st speed	0 - 450 min ⁻¹
Battery voltage	18 V
maximum twist drill size Ø in steel	13 mm
maximum torque hard	60 Nm
Type of rechargeable battery	Lithium-ion
Type of product	limpact drill /screwdriver