

# AEG

## Cordless rotary hammer, Type: BBH18BL2-5



### Order data

Order number	075535 BBH18BL2-5
GTIN	4058546417109
Item class	07A

### Description

#### Version:

- **Brushless 18 V cordless rotary hammer with sturdy metal gearbox casing and SDS-plus tool holder.**
- **Safety shut-off.**
- **Impact action can be switched off for drilling wood and metals.**
- **Zero rotation for easy chisel work.**
- **Handle with anti-vibration system.**

#### Supplied with:

Includes 2 pcs. 18 V / 5.0 Ah Li-ion batteries, charger, and transport case.

### Technical description

suitable battery - supplier / battery type / voltage	AEG type AS 18 V
Power supply	Battery-powered
Packaging	Carrying case
maximum twist drill size $\varnothing$ in concrete	26 mm

Battery capacity	5 A·h
maximum twist drill size Ø in steel	13 mm
Tool arbor shape	SDS Plus
Type of rechargeable battery	Lithium-ion
maximum hammer rate	5000 min <sup>-1</sup>
Manufacturer's designation	BBH18BL2
Impact energy	2.5 J
maximum twist drill size Ø in wood	30 mm
maximum vibration to EN	18.3 m/s <sup>2</sup>
Number of rechargeable batteries contained	2
Battery voltage	18 V
Weight	3 kg
maximum speed 1st speed	0 - 1500 min <sup>-1</sup>
Type of product	Hammer drill