



Temperature measuring device without measuring sensor, Type: 925



Order data

Order number	474111 925
GTIN	4029547025778
Item class	47B

Description

Version:

Compact temperature measuring device with app connection for simple, quick and precise temperature measurement in industry and trade.

Supplied with:

Supplied with 3 batteries No. 081561 size LR6, test certificate, TE type K sensor, transport case.

Technical description

Width	60 mm
Manufacturer's designation	925
Error limit	$\pm 0.5 + 0.3$ % of the measured value (at -50 to 1000°C) °C
Measuring range temperature (sensor type K)	-50 - 1000 °C
Number of batteries contained	3
Article no of the battery / rechargeable battery fitted	081561 LR6

Height	28 mm
Length	135 mm
Power supply	Battery-powered
Resolution	0.1 / 1 (from +500) °C
Calibration	I8
Type of product	Temperature measuring device

Services

CalibrationTemperature display unit Number of inlets 1	027500 1
DAkkS calibrationCalibration temperature display unit Number of inlets 1	027510 1

Accessories

Temperature sensor Type K Type OF	474120 OF
Temperature sensor Type K Type EF	474120 EF