

FLUKE.

Clamp meter, Type: 378FC**Order data**

Order number	473290 378FC
GTIN	195112002148
Item class	47H

Description**Version:**

Current clamps with large easy-to-read LCD display in a slim and ergonomic design. Non-contact voltage and current measurement with the Fieldsense™ technology. Fluke Connect software for recording and analysing measurement results. Measurement of extremely high currents with the flexible iFlex® current transformer.

Standard:**EN 61010-1****Supplied with:**

Incl. test leads and padded carrying case. Batteries 2 pcs. No. 081561 size LR6.

Technical description

Capacitance	100.0 μ F up to 1000 μ F
Information displayed	6000
Overvoltage category	CAT III 1000 V
Overvoltage category	CAT IV 600 V
Resistance	0.1 Ω – 60 k Ω

AC current	0.1 A – 2500 A
Number of batteries contained	2
AC voltage	0.1 V – 1000 V
Frequency	5 Hz – 500 Hz
Basic accuracy	2 %
Power supply	Battery-powered
maximum jaw aperture	34 mm
Article no of the battery / rechargeable battery fitted	081561 LR6
Memory function	HOLD, MAX/MIN
Measurement process	TRUE RMS (AC)
DC voltage	0.1 V – 1000 V
DC current	0.1 A – 1000 A
Standard	EN 61010-1
Calibration	I4
Type of product	Current clamp

Services

CalibrationClamp meter Type D	027050 D
DAkkS calibrationClamp meter Type D	027060 D