

BENNING**Multimeter, Manufacturer's designation: MM2****Order data**

Order number	473300 MM2
GTIN	4014651000520
Item class	47A

Description**Version:**

Sturdy plastic casing with large-format, 3½ inch, 4 inch or 4¾ inch LCD display.

Application:

Digital service multimeters for a wide range of applications. These provide a high level of safety and other additional functions. Precise current measurement ranges (200 µA and 2/20/200 mA) for ionization current measurement on the gas burner and for testing the sacrificial anode in the boiler (heating and air conditioning technicians).

Standard:

IEC / DIN EN 061010-1 (DIN VDE 0411-1).

Supplied with:

Batteries, probe leads, compact protective case, operating instructions. Rubber protective surround.

Technical description

Number of batteries contained	2
Calibration	I3
DC voltage	100 µV – 1000 V

Measurement process	RMS
Continuity testing	yes
Diode testing	yes
Resistance	0.1 Ω – 20 M Ω
AC current	0.1 μ A – 20 A
DC current	0.1 μ A – 20 A
Information displayed	2000
Article no of the battery / rechargeable battery fitted	081561 6LR61
Overvoltage category	CAT III 600 V
Overvoltage category	CAT II 1000 V
Basic accuracy	0.5 %
AC voltage	100 μ V – 750 V
Power supply	Battery-powered
Material of the housing	Plastic
Type of product	Multimeter

Services

CalibrationDigital multimeter Number of decimal places 3	027000 3
DAkkS calibrationDigital multimeter Number of decimal places 3	027010 3

Accessories

Alkaline-manganese batteries International size 6LR61	081561 6LR61
---	--------------