

BENNING**Multimeter, Manufacturer's designation: MM2-1****Order data**

Order number	473300 MM2-1
GTIN	4014651446915
Item class	47A

Description**Version:**

Sturdy plastic casing with large-format, 3½ inch, 4 inch or 4¾ inch LCD display.

Application:

Digital service multimeters for a wide range of applications. These provide a high level of safety and other additional functions. The entry-level category into professional measurement technology. Optimum price-performance ratio. Quick continuity test, socket check with warning (fuse protection).

Standard:

IEC / DIN EN 061010-1 (DIN VDE 0411-1).

Supplied with:

Batteries, probe leads, compact protective case, operating instructions. Rubber protective surround.

Technical description

DC voltage	10 μ V – 1000 V
Information displayed	6000
Calibration	I3

Memory function	HOLD, MAX / MIN / AVG, REL
Power supply	Battery-powered
Resistance	0.1 Ω – 60 M Ω
Article no of the battery / rechargeable battery fitted	081561 LR3
Diode testing	yes
Overvoltage category	CAT IV 600 V
Overvoltage category	CAT IV 600 V
Voltage sensor (non-contact)	yes
AC voltage	10 μ V – 1000 V
Measurement process	TRUE RMS
Number of batteries contained	2
Continuity testing	yes
Frequency	10 Hz – 1 kHz
Basic accuracy	0.2 %
Material of the housing	Plastic
Type of product	Multimeter

Services

CalibrationDigital multimeter Number of decimal places 3	027000 3
DAkkS calibrationDigital multimeter Number of decimal places 3	027010 3

Accessories

Alkaline-manganese batteries International size LR3	081561 LR3
---	------------