

**BENNING****Multimeter, Manufacturer's designation: MM2-3****Order data**

Order number	473300 MM2-3
GTIN	4014651446939
Item class	47A

**Description****Version:**

Sturdy plastic casing with large-format, 3½ inch, 4 inch or 4¾ inch LCD display.

**Application:**

Digital service multimeters for a wide range of applications. These provide a high level of safety and other additional functions. The entry-level category into professional measurement technology. Optimum price-performance ratio. Quick continuity test, socket check with warning (fuse protection).

**Standard:**

**IEC / DIN EN 061010-1 (DIN VDE 0411-1).**

**Supplied with:**

Batteries, probe leads, compact protective case, operating instructions. Wire temperature sensor, rubber protective frame.

**Technical description**

AC current	1 mA – 10 A
Resistance	0.1 Ω – 60 MΩ
Calibration	I3

Calibration	17
Basic accuracy	0.2 %
Frequency	10 Hz – 1 kHz
Temperature	-40 - 400 °C
DC voltage	10 µV – 1000 V
AC voltage	10 µV – 1000 V
Voltage sensor (non-contact)	yes
Capacitance	0.01 nF – 10 mF
Number of batteries contained	2
Measurement process	TRUE RMS
Power supply	Battery-powered
Diode testing	yes
Continuity testing	yes
DC current	1 mA – 10 A
Memory function	HOLD, MAX / MIN / AVG, REL
Overvoltage category	CAT IV 600 V
Overvoltage category	CAT IV 600 V
Information displayed	6000
Article no of the battery / rechargeable battery fitted	081561 LR3
Material of the housing	Plastic
Type of product	Multimeter

## Services

DAkkS calibrationDigital multimeter Number of decimal places 3	027010 3
CalibrationDigital multimeter Number of decimal places 3	027000 3
CalibrationTemperature sensor with / without display Type A	027520 A
DAkkS calibrationTemperature sensor with / without display Type A	027540 A

---

## Accessories

Alkaline-manganese batteries International size LR3

081561 LR3