

FLUKE.

Multimeter, Type: 115**Order data**

Order number	473322 115
GTIN	095969344814
Item class	47H

Description**Version:**

Ergonomic plastic housing with integral holster. Large LCD display for good legibility. Reliable and easy to use – **warning if the test leads are connected wrongly**. Thanks to its simple operation, it is ideal for use in mobile services.

Function:

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

Application:

Digital service multimeters for a wide range of applications, very high safety and other additional functions.

Standard:

IEC 61010; ANSI/ISA S82.02.01; CSA C22.2-1010.1

Supplied with:

Battery 081561 6LR61, test leads, and removable insulating caps.

Technical description

Measurement process	TRUE RMS
---------------------	----------

Display backlit	no
Continuity testing	yes
IP Index of Protection	IP 67
Resistance	0.1 Ω – 40 M Ω
DC voltage	0.1 mV – 600 V
Capacitance	1 nF – 1 mF
Overvoltage category	CAT III 600 V
Information displayed	6000
AC current	0.1 mA – 10 A
Number of batteries contained	1
Frequency	0.01 Hz – 50 kHz
Power supply	Battery-powered
Diode testing	yes
AC voltage	0.1 mV – 600 V
Article no of the battery / rechargeable battery fitted	081561 6LR61
DC current	0.1 mA – 10 A
Basic accuracy	0.05 %
Calibration	I3
Type of product	Multimeter

Services

DAkKS calibrationDigital multimeter Number of decimal places 3	027010 3
CalibrationDigital multimeter Number of decimal places 3	027000 3

Accessories

Alkaline-manganese batteries International size 6LR61	081561 6LR61
---	--------------