

**metabo****Cordless impact wrench without rechargeable battery, Type: 18LTX1750****Order data**

Order number	074061 18LTX1750
GTIN	4061792202450
Item class	03D

**Description****Version:****High torques for heavy-duty screwdriving applications.**

The LTX-class cordless impact wrenches are available with a maximum torque of 300 Nm, 800 Nm or 1750 Nm. Perfectly suited for power-intensive screwdriving in all performance ranges. They are also equipped with an Automatic Power Shift (APS) mode:

- **Unscrewing in APS mode: prevents the screw/nut from falling through automatic reduction of speed after loosening.**
- **Bolting in APS mode: prevents the screw/nut from overturning through automatic switching off after the first impact.**

By the way, all Metabo battery packs come with a 3-year warranty, irrespective of the number of charging cycles.

Further details such as the bright LED work light ensure even more comfort when working.

- **Extremely powerful cordless impact wrench with 3/4 inch external square drive and 1750 Nm.**
- **Unique Metabo brushless motor for quick working and maximum efficiency with every use.**
- **Overload protection to protect the motor against overheating.**
- **Very powerful for heavy screwdriving applications.**
- **Low-recoil operation with very high torque.**
- **Twelve speed/torque levels for a wide range of applications.**

- **Integrated work light to illuminate the workplace.**
- **Sturdy die-cast aluminium gearbox casing for optimum heat dissipation and a long service life.**

**Advantage:**

**Batteries are 100% compatible – now also across different manufacturers.**

All 18 V devices and battery packs from CAS partners are 100% compatible with each other. CAS stands for "Cordless Alliance System".

**Supplied with:**

Without battery, charger or transport case.

**Note:**

See No. 073870 – 073890 for suitable batteries and chargers.

## Technical description

Number of rechargeable batteries contained	0
Torque settings	12
Tool arbor size	3/4 in
maximum torque	1750 Nm
Motor design	brushless
suitable battery - supplier / battery type / voltage	Type CAS 18 V
Battery voltage	18 V
Packaging	Metabox
typical application	Heavy Duty
Toolholder	External square drive
maximum break-away torque	2100 Nm
Manufacturer's designation	SSW 18 LTX 1750 BL
Type of rechargeable battery	Lithium-ion
Power supply	Mains operated
Weight without battery	3 kg
maximum hammer rate	2450 min <sup>-1</sup>
No load speed	0 - 1650 min <sup>-1</sup>
Type of product	Impact wrench

