

**HOLEX****Garment locker with fitted base and security twist bar lock, Number of compartments: 3****Order data**

Order number	949613 3
GTIN	4067263642657
Item class	92S

**Description****Version:**

Garment locker with compartment width 300 mm with welded-in hat shelf. Hanger rail has 3 sliding clothes hooks. Door with diamond pattern ventilation holes and label frame.

With base.

With security twist bar lock; lockable with a padlock (not included in scope of delivery).

**Ventilation concept:** Air flows through holes in the rear of the cabinet floor ensuring good ventilation and drying within the compartment. Air infeed for special cabinets with fitted bases is via openings above the recessed base.

**Standard:**

**DIN 4547**

**Colour:**

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**. No special paint finishes available.

**Note:**

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

**Technical description**

usable depth of each compartment	477 mm
Support cabinet version	Fitted base
Nameplate	no
Weight	52 kg
Shelf width	298 mm
usable height of each hat compartment	328 mm
usable height of each clothing compartment	1420 mm
Storage shelf depth	477 mm
for padlock with shackle Ø up to	6 mm
usable width of each compartment	240 mm
Height	1950 mm
Depth	500 mm
Sloping roof	no
Ventilation slots in the door	yes
Lock version	Security twist bar lock
for padlock	yes
Standard	DIN 4547
Special paints available	no
Number of clothes rails	1
Number of compartments	3
Cabinet fronts	Plain sheet metal swing door
Width	900 mm
Number of fixed shelves	1
Material thickness	0.8 mm
Door opening angle	110 degrees
Colour selection	RAL 7035, RAL 7016, RAL 5005
Type of product	Locker

