

HOLEX**Garment locker with a sloping top, fitted base and security twist bar lock,
Number of compartments: 2****Order data**

Order number	949631 2
GTIN	4067263642763
Item class	92S

Description**Version:**

Garment locker with sloping roof attachment, which prevents objects from being left lying on top of the locker. Compartment width 300 mm with welded-in hat shelf. Hanger rail has 3 sliding clothes hooks. Door with diamond pattern ventilation holes and label frame.

With base.

With security twist bar lock; lockable with a padlock (not included in scope of delivery).

Standard:

DIN 4547

Colour:

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**. No special paint finishes available.

Note:

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

usable width of each compartment	240 mm
Number of compartments	2
usable height of each hat compartment with sloping roof	328 mm
Height at the front	1950 mm
usable height of each clothing compartment	1420 mm
Special paints available	no
for padlock	yes
Number of fixed shelves	1
Storage shelf depth	477 mm
for padlock with shackle Ø up to	6 mm
usable depth of each compartment	477 mm
Standard	DIN 4547
Cabinet fronts	Plain sheet metal swing door
Shelf width	298 mm
Height at the rear	2180 mm
Support cabinet version	Fitted base
Number of clothes rails	1
Ventilation slots in the door	yes
Lock version	Security twist bar lock
Depth	500 mm
Width	600 mm
Sloping roof	yes
Weight	42 kg
Material thickness	0.8 mm
Door opening angle	110 degrees
Colour selection	RAL 7035, RAL 7016, RAL 5005
Type of product	Locker

