



Garment locker with a sloping top, plastic feet and security twist bar lock, Number of compartments: 4

Order data

Order number	949633 4
GTIN	4067263642848
Item class	92S

Description

Version:

Garment locker with sloping roof attachment, which prevents objects from being left lying on top of the locker. Compartment width 300 mm with welded-in hat shelf. Hanger rail has 3 sliding clothes hooks. Door with diamond pattern ventilation holes and label frame.

With plastic feet.

With security twist bar lock; lockable with a padlock (not included in scope of delivery).

Standard:

DIN 4547

Colour:

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**. No special paint finishes available.

Note:

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Standard	DIN 4547
Cabinet fronts	Plain sheet metal swing door
Ventilation slots in the door	yes
usable depth of each compartment	477 mm
Shelf width	298 mm
Height at the front	1950 mm
Weight	75 kg

Special paints available	no
Height at the rear	2180 mm
Number of fixed shelves	1
Number of compartments	4
Sloping roof	yes
Lock version	Security twist bar lock
for padlock	yes
for padlock with shackle Ø up to	6 mm
Number of clothes rails	1
Width	1200 mm
Support cabinet version	Steel feet
usable height of each hat compartment with sloping roof	328 mm
Depth	500 mm
usable height of each clothing compartment	1420 mm
Storage shelf depth	477 mm
usable width of each compartment	240 mm
Material thickness	0.8 mm
Door opening angle	110 degrees
Colour selection	RAL 7035, RAL 7016, RAL 5005
Type of product	Locker