

Garant
GARANT Master Mute cutting head, right-hand, System / insert size: DM/3

Order data

Order number	264838 DM/3
GTIN	4067263707868
Item class	29D

Description
Suitable for:

Boring bar shanks No. 264930, 264934 and 264938.

Note:

Combination of all cutting heads with all boring bar shanks within the same system (GL, QC, DM) possible.

Through-coolant: yes

System: DM

Cutting point / joint: 40 mm

ISO code cutting head: PTFNR

suitable indexable insert: TN.. 1604..

Approach angle: 91 °

Minimum pre-drill $\varnothing D_{\min}$: 50 mm

Centre offset L_3 : 27 mm

Technical description

Minimum pre-drill $\varnothing D_{\min}$	50 mm
Centre offset L_3	27 mm

suitable indexable insert	TN.. 1604..
Approach angle	91 °
Shim	269005 15
Lever screw	259018 19
Lever	259015 20
Cutting point / joint	40 mm
Overall length L	26 mm
Series	Master Mute
ISO code cutting head	PTFNR
System	DM
Application type	right-hand
Through-coolant	yes
Type of product	Cutting head