

Garant**GARANT Master Mute cutting head, right-hand, System / insert size: DM/6****Order data**

Order number	264838 DM/6
GTIN	4067263707899
Item class	29D

Description**Suitable for:**

Boring bar shanks No. 264930, 264934 and 264938.

Note:

Combination of all cutting heads with all boring bar shanks within the same system (GL, QC, DM) possible.

Through-coolant: yes

System: DM

Cutting point / joint: 40 mm

ISO code cutting head: SDUCR

suitable indexable insert: DC.. 11T3..

Approach angle: 93 °

Minimum pre-drill $\varnothing D_{\min}$: 50 mm

Centre offset L_3 : 27 mm

Technical description

Insert screw	269028 50
Cutting point / joint	40 mm

Centre offset L ₃	27 mm
ISO code cutting head	SDUCR
Series	Master Mute
System	DM
Overall length L	32 mm
suitable indexable insert	DC.. 11T3..
Minimum pre-drill $\varnothing D_{\min}$	50 mm
Approach angle	93 °
Application type	right-hand
Through-coolant	yes
Type of product	Cutting head