



## Telescopic ratchet, 1/2 inch extendable, Type: 1/2



### Order data

Order number	640288 1/2
GTIN	4018754336388
Item class	63A

### Description

#### Version:

Fixing is performed by the locking ring. With reversing lever for right-hand and left-hand threads. Convenient, simple and fast adjustment of the lengths using a rocker switch, even one-handed. Five latch steps with extension lengths of 410 mm, 465 mm, 520 mm, 575 mm and 630 mm. Maximum permissible torque 512 Nm.

Material selection and special forging process guarantee optimal functioning and long life.

#### Standard:

Außenvierkant nach **DIN 3120-A 12,5** mit federnder Kugel.

#### Suitable for:

Manual use.

### Technical description

Square drive	1/2 in
Standard	DIN 3122
overall length	410 - 630 mm
No. of teeth	36
Working angle	10 degrees
Material	Chrome alloy steel
Surface	chrome-plated
with ejector	no
Ratchet head can be detached from the handle	no
Twist handle	no

stepless pull-out	no
Mounting hole at the end of the handle	no
Type of product	Ratchet