

**Cordless impact wrench / impact driver, Type: GDS18450HC****Order data**

Order number	074052 GDS18450HC
GTIN	4059952568034
Item class	03B

Description**Version:**

Cordless impact wrench / impact driver.

- **Reversible.**
 - **Battery charge display.**
- 1/2-inch impact wrench with Bluetooth connectivity.
- **2 operating modes for metal and wood. Further parameters can be set individually using the Toolbox app.**

Supplied with:

Supplied with 2× Li-ion batteries, charger, L-BOXX

Note:

Suitable replacement batteries and chargers can be found under No. 073851 – 073867.

Technical description

Manufacturer's designation	GDS 18V-450 HC
maximum speed 1st speed	1500 min ⁻¹
No load speed	1000 min ⁻¹

No load speed	1500 min ⁻¹
No load speed	2300 min ⁻¹
Number of rechargeable batteries contained	2
Packaging	Modular case (L-Boxx)
maximum torque 2nd step	330 Nm
Tool arbor drive profile	External square drive
Number of impacts	0 - 3300 min ⁻¹
Number of impacts 2nd stage	2500 min ⁻¹
Number of impacts 3rd stage	3300 min ⁻¹
Weight without battery	1.6 kg
Power supply	Mains operated
maximum torque 3rd step	450 Nm
maximum vibration to EN	14.5 m/s ²
maximum torque 1st step	250 Nm
Battery capacity	4 Ah
Battery voltage	18 V
Number of impacts 1st stage	1900 min ⁻¹
suitable battery - supplier / battery type / voltage	Bosch 18 V
Weight	2.1 kg
Type of rechargeable battery	Lithium-ion
maximum speed 2nd speed	2300 min ⁻¹
maximum torque hard	450 Nm
maximum break-away torque	800 Nm
maximum screw Ø (8.8 - 12.9)	M20
Tool arbor size	1/2 in
typical application	Heavy Duty
Type of product	Impact wrench

