

**Cordless hand-held circular saw, Type: GKM18V50****Order data**

Order number	078183 GKM18V50
GTIN	4059952548371
Item class	03B

Description**Version:**

Cordless circular metal saw for fast and precise cuts, virtually no sparks.

- **Integrated, robust chip collection box for excellent occupational safety and clean surfaces.**
- **Precise cuts thanks to cutting line indicator, viewing window and integrated LED light.**
- **Mountable parallel stop to perfectly guide longitudinal cuts.**

Supplied with:

Includes 2 pcs. 18 V 5 Ah rechargeable battery, charger, parallel stop and L-BOXX.

Note:

Circular saw blades can be found under 583920.

See from No. 073851 and No. 073866 for suitable spare batteries and chargers.

Technical description

Power supply	Mains operated
Weight	2.2 kg
Battery capacity	5 Ah
Saw blade Ø	136 mm
maximum cutting depth 90°	50 mm
Saw blade bore Ø	20 mm
Battery voltage	18 V

Manufacturer's designation	GKM 18V-50
Type of rechargeable battery	Lithium-ion
maximum speed	4250 min ⁻¹
suitable battery - supplier / battery type / voltage	Bosch 18 V
Number of rechargeable batteries contained	2
Version	Metal cutting circular saw
Packaging	Modular case (L-Boxx)
Type of product	Saw