



Angled die grinder Cordless, Type: GWG12V-50



Order data

Order number	077260 GWG12V-50
GTIN	4059952634166
Item class	03C

Description

Version:

Cordless compact grinder for 50 mm discs. Variable speed trigger switch and five different speed modes provide optimum speed control. Compact, cordless and powerful – The 12V grinder suitable for a wide range of applications.

- **High performance for fast results: powerful brushless high-performance motor and constant high torque ensure high productivity.**
- **Fatigue-free working even in confined areas: extremely light and compact design with a small handle for easy grinding.**
- **Perfect speed control for different applications and ideal results: variable speed trigger switch and five different speed modes enable optimum speed control.**

Supplied with:

Without battery and charger, 1 pc. 6 mm collet.

Note:

Suitable grinding discs (CER) can be found from No. 554012, for cleaning discs and coarse cleaning discs see No. 554050; 554051; 554054 and 554055.

Technical description

Battery voltage	12 V
-----------------	------

Power supply	Mains operated
Number of rechargeable batteries contained	0
Weight	0.53 kg
Manufacturer's designation	GWG 12V-50 S
Dead man's circuit	no
suitable battery - supplier / battery type / voltage	Bosch 12 V
Type of rechargeable battery	Lithium-ion
maximum disc Ø	50 mm
Speed range	5000 - 15000 min ⁻¹
maximum collet Ø	6 mm
Type of product	Angle grinder