

**Straight die grinder Cordless, Type: GGS18V-20****Order data**

Order number	077267 GGS18V-20
GTIN	4059952623832
Item class	03B

Description**Version:**

Compact **cordless straight grinder** with brushless motor, overload protection and restart protection.

Supplied with:

Without battery, without charger. Including 2 open-ended spanners AF 19.

Technical description

Weight	1.2 kg
Manufacturer's designation	GGG 18V20
Type of rechargeable battery	Lithium-ion
Power supply	Mains operated
suitable battery - supplier / battery type / voltage	Bosch 18 V
electronic speed pre-selection	no
Number of rechargeable batteries contained	0
maximum collet \varnothing	8 mm
Speed range	24000 min ⁻¹
Battery voltage	18 V

Packaging	Modular case (L-Boxx)
Type of product	Straight die grinder

Accessories

Battery charger Type 1880CV	073866 1880CV
Li-ion battery Battery type, battery voltage B18 V	073854 B18