

metabo**Bench grinder 230 V, Type: DS150P****Order data**

Order number	077530 DS150P
GTIN	4061792225992
Item class	03D

Description**Version:**

Bench grinder for grinding, sharpening, deburring and, if using a steel wire brush, also removing rust on steel and metals. The integrated LED light optimally illuminates the working area.

Durable discs and very smooth running thanks to the high-quality mounting flanges.

- **Workpiece supports can be adjusted without tools.**
- **Powerful machine for demanding sharpening, grinding and deburring work.**
- **Suitable for the use of round steel wire brushes for removing rust.**
- **Integrated LED light to optimally illuminate the work area.**
- **Quiet, low-vibration, maintenance-free induction motor.**
- **Maximum smooth running and long tool life of the discs thanks to high-quality mounting flanges.**
- **The highest level of safety at work thanks to extra-large, sturdy spark protection glass.**

Supplied with:

Includes standard aluminium oxide grinding wheels 36 P and 60 N, spark protection glass, workpiece rest and hexagon key.

Note:

Suitable grinding wheels can be found under No. 596100 and No. 568733.

Technical description

Abrasive disc width T	20 mm
-----------------------	-------

Power supply	Mains-powered
maximum speed	2980 min ⁻¹
Power consumption	400 W
Abrasive disc Ø D	150 mm
Manufacturer's designation	DS 150 Plus
Abrasive disc hole Ø H	20 mm
Weight	10.2 kg
Cable length	1.8 m
Rated power	230 V