

melabo**Cordless jigsaw without rechargeable battery, Type: 18LTX100****Order data**

Order number	078185 18LTX100
GTIN	4007430324603
Item class	03D

Description**Version:**

Robust and extremely easy to use cordless jigsaw for **precise cuts**.

- **Variable stroke rate, pendulum stroke and low-lying, spring-assisted saw blade guidance.**
- **Switchable chip blowing function ensures a clear view of the interface.**
- **Small handle circumference and softgrip surface.**

Advantage:

Batteries are 100% compatible – now also across different manufacturers.

All 18 V devices and battery packs from CAS partners are 100% compatible with each other. CAS stands for "Cordless Alliance System".

Supplied with:

Without battery and charger, including suction nozzle, protective glass and hexagon key.
Supplied with chip break guard.

Note:

See No. 073870 – 073890 for suitable batteries and chargers.

Technical description

Manufacturer's designation	STA 18 LTX 100
----------------------------	----------------

tool change without tools	Yes, Metabo Quick
Format	Straight handle
Special features	Small handle circumference
Orbital stroke	4-fold
Power supply	Mains operated
maximum sawn thickness steel	10 mm
suitable battery - supplier / battery type / voltage	Type CAS 18 V
Weight	1.9 kg
Battery voltage	18 V
Mitre angle adjustment	yes
maximum sawn thickness wood	100 mm
maximum vibration to EN	11.8 m/s ²
Number of rechargeable batteries contained	0
Rate of strokes	550 - 2800 min ⁻¹
Type of rechargeable battery	Lithium-ion
Type of product	Saw