

**metabo**
**Cordless sabre saw without battery, Type: SSE18LTXBL**

**Order data**

Order number	078223 SSE18LTXBL
GTIN	4061792172524
Item class	03D

**Description**
**Version:**

Powerful cordless sabre saw with low weight and angled softgrip handle for high working comfort.

- **Brushless motor for quick work progress and maximum efficiency.**
- **Depth stop adjustment without using tools.**
- **Vario (V) electronics for working at material-appropriate stroke rate.**
- **Saw blade can be rotated 180° for comfortable working above the head.**
- **Metabo Quick to change saw blades without the need for any tools.**
- **Selectable orbital stroke.**

**Advantage:**

**100% compatibility of the batteries – now also cross-manufacturer.**

All 18 V devices and battery packs from CAS partners are 100% compatible with each other. CAS stands for "Cordless Alliance System".

**Supplied with:**

Without battery and charger, in a cardboard box.

**Note:**

Sabre saw blades can be found from No. 588600.

See No. 073870 – No. 073890 for suitable batteries and chargers.

**Technical description**

suitable battery - supplier / battery type / voltage	Type CAS 18 V
maximum vibration to EN	27.5 m/s <sup>2</sup>

Rate of strokes	0 - 2700 min <sup>-1</sup>
Weight	3.1 kg
Battery capacity	5.2 Ah
Number of rechargeable batteries contained	2
Manufacturer's designation	SSE 18 LTX BL
Power supply	Mains operated
Stroke length	32 mm
Type of rechargeable battery	Lithium-ion
Battery voltage	18 V
Packaging	Metabox
Type of product	Saw

## Accessories

Battery packLi-Power Battery capacity 2 A·h	073870 2
Battery packLi-Power Battery capacity 5,2 A·h	073870 5,2
Battery charger Type ASC55	073890 ASC55
Battery packLi-Power Battery capacity 4 A·h	073870 4