

metabo
Sabre saw, Type: SSEP1400

Order data

Order number	078222 SSEP1400
GTIN	4007430292995
Item class	03D

Description
Version:

Powerful 1400 W sabre saw with stroke rate held constant for the toughest applications.

- **Switchable 3-stage pendulum stroke for optimum sawing performance in any material.**
- **Saw blade can be rotated 180° for comfortable overhead work.**
- **Metabo VibraTech (MVT): Integrated mass compensation to reduce vibrations.**

Supplied with:

Transport case, saw blade.

Note:

Sabre saw blades can be found from No. 588600.

Technical description

maximum vibration to EN	12.9 m/s ²
Stroke length	32 mm
Manufacturer's designation	SSEP 1400 MVT
AC supply voltage	230 V
Power consumption	1400 W
Mains frequency	50 Hz
Rate of strokes	0 - 2800 min ⁻¹
Special features	Metabo Quick
Packaging	Carrying case

Anti-vibration system	yes
Weight	4.6 kg
Power supply	Mains-powered
Type of product	Saw