


TNMG 160404, Grade: CCX

Order data

Order number	251472 CCX
GTIN	4960664900398
Item class	25E

Technical description

Cutting depth a_p	0.2 - 1.5 mm
Coating	coated
Grade	CCX
Chip breaker	PP
Main application	P
Finishing/roughing assignment	Finishing
Corner radius	0.4 mm
Cutting conditions	continuous
Feed f	0.05 - 0.35 mm/rev.
Tool material	Cermet
Number of changes/inserts	6
Cutting speed v_c main application	210 - 450 m/min

ISO code indexable insert	TNMG 160404
Type of product	Indexable insert for turning