


CC.T 060202, Grade: CCX

Order data

Order number	260091 CCX
GTIN	4960664911196
Item class	25E

Description

CC.T 060202 CCX Grade: CCX
 Chip breaker: PP
 Tolerance: M
 Cutting depth a_p : 0.1 - 0.8 mm
 Feed f : 0.05 - 0.3 mm/rev.
 Cutting speed v_c main application: 120 - 310 m/min

Technical description

Cutting conditions	continuous
Tool material	Cermet
Main application	P
ISO code indexable insert	CCMT 060202
Chip breaker	PP
Feed f	0.05 - 0.3 mm/rev.
Tolerance	M

Finishing/roughing assignment	Finishing
Coating	coated
Corner radius	0.2 mm
Grade	CCX
Number of changes/inserts	2
Cutting speed v_c main application	120 - 310 m/min
Cutting depth a_p	0.1 - 0.8 mm
Type of product	Indexable insert for turning