

**CC.T 060204, Grade: CCX****Order data**

Order number	260092 CCX
GTIN	4960664911202
Item class	25E

**Description**

CC.T 060204 CCX Grade: CCX  
Chip breaker: PP  
Tolerance: M  
Cutting depth  $a_p$ : 0.1 - 0.8 mm  
Feed  $f$ : 0.05 - 0.3 mm/rev.  
Cutting speed  $v_c$  main application: 120 - 310 m/min

**Technical description**

Cutting speed $v_c$ main application	120 - 310 m/min
Chip breaker	PP
Finishing/roughing assignment	Finishing
Tolerance	M
Grade	CCX
Number of changes/inserts	2
Tool material	Cermet

Main application	P
Cutting depth $a_p$	0.1 - 0.8 mm
Feed f	0.05 - 0.3 mm/rev.
Corner radius	0.4 mm
ISO code indexable insert	CC.T 060202
Coating	coated
Cutting conditions	continuous
Type of product	Indexable insert for turning