

HOLEX

Garment locker with base and sloping roof attachment, for clean & dirty separation and security twist bar lock, Number of compartments: 4



Order data

Order number	949732 4
GTIN	4067263828792
Item class	92S

Description

Version:

Garment locker with extra wide split compartment, for clean & dirty separation. The partition within a compartment is for hygienic separation of street clothes and work clothes. The two swing doors close to each other and are centrally locked with a single lock. Doors with diamond pattern ventilation holes and label frame. With welded-in hat shelf. Hanger rail with 3 sliding clothes hooks.

With base.

With security twist bar lock; lockable with a padlock (not included in scope of delivery).

Standard:

DIN 4547

Colour:

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**. No special paint finishes available.

Note:

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

usable depth of each compartment	477 mm
Shelf width	298 mm
Height at the rear	2180 mm
usable height of each clothing compartment	1420 mm
Width	1200 mm
Height at the front	1950 mm
Depth	500 mm
Weight	75 kg
usable height of each hat compartment with sloping roof	328 - 530 mm
Storage shelf depth	477 mm
usable width of each compartment	2 × 240 mm
Material thickness	0.8 mm
Door opening angle	110 degrees
Colour selection	RAL 7035, RAL 7016, RAL 5005
Type of product	Locker