

metabo**Bench grinder 400 V, Type: DSD200P****Order data**

| | |
|--------------|----------------|
| Order number | 077541 DSD200P |
| GTIN | 4061792226043 |
| Item class | 03D |

Description**Version:**

Bench grinder for grinding, sharpening, deburring and, if using a steel wire brush, also removing rust on steel and metals. The integrated LED light optimally illuminates the working area. Durable discs and very smooth running thanks to the high-quality mounting flanges.

- **Workpiece rests can be adjusted without tools.**
- **Bench grinder with three-phase motor offers particularly high torque and is suitable for high loads.**
- **Extraction connection on both sides, suitable for common coupling bushes.**
- **Large, tilting tool support with handy V-groove for sharpening welding needles.**
- **For grinding, sharpening, deburring and removing rust on steel and metals.**
- **Suitable for the use of round steel wire brushes for removing rust.**
- **Integrated LED light to optimally illuminate the work area.**
- **Quiet, low-vibration, maintenance-free induction motor.**
- **Maximum smooth running and long tool life of the discs thanks to high-quality mounting flanges.**
- **Restart protection: prevents unintentional start-up after power interruption.**

Supplied with:

Includes standard aluminium oxide grinding wheels 36 P and 60 N, spark protection glass, workpiece rest and hexagon key.

Note:

Suitable grinding wheels can be found under No. 596100 and No. 568733.

Technical description

| | |
|------------------------------------|-------------------------|
| Power consumption | 750 W |
| Abrasive disc hole \varnothing H | 32 mm |
| Weight | 17.8 kg |
| Abrasive disc width T | 25 mm |
| maximum speed | 2980 min ⁻¹ |
| Manufacturer's designation | DSD 200 Plus |
| Abrasive disc \varnothing D | 200 mm |
| Power supply | Mains-powered |
| Cable length | 1.8 m |
| Rated power | 400 V |
| Type of product | Double grinding machine |