

metabo**Cordless metal cutting circular saw without rechargeable battery, Type: MKS18LTX58****Order data**

Order number	078188 MKS18LTX58
GTIN	4061792005570
Item class	03D

Description**Version:**

Powerful cordless metal hand-held circular saw with chip capture box for cold sawing on metals. Compatible with guide rails.

- **Run-out brake for maximum safety as saw blade is stopped fast (< 1 sec.).**
- **Fast and precise cutting of pipes, profiles, ducts, metal lattices and sheets. No sparks or burrs.**
- **With chip capture box to ensure a clean working environment.**
- **Robust saw with protective hood made of die-cast aluminium and base plate made of stainless steel.**
- **Lightweight and compact, ergonomic design.**
- **Viewing window in the protective hood for precise cutting.**
- **Stepless cutting depth adjustment mechanism according to mm and inch scale, requires no tools.**
- **Conveniently change the saw blade thanks to spindle lock.**
- **Precise straight cutting of metal lattices and steel and profiled sheets thanks to guide rail (accessory).**

Advantage:

Batteries are 100% compatible – now also across different manufacturers.

All 18 V devices and battery packs from CAS partners are 100% compatible with each other. CAS stands for "Cordless Alliance System".

Supplied with:

Without battery and charger, including carbide circular saw blade for metal (40 teeth), parallel stop, hexagon key and guide rail adapter.

Note:

See No. 073870 – 073890 for suitable batteries and chargers.

Technical description

Saw blade bore Ø	20 mm
Manufacturer's designation	MKS 18 LTX 58
Weight including rechargeable battery	3.7 kg
maximum cutting depth 90°	58 mm
Saw blade Ø	165 mm
Weight without battery	2.8 kg
Battery voltage	18 V
Power supply	Mains operated
Number of rechargeable batteries contained	0
suitable battery - supplier / battery type / voltage	Type CAS 18 V
Type of rechargeable battery	Lithium-ion
Type of product	Saw