

metabo**Combo bench grinder 230 V, Type: BS200P****Order data**

Order number	077550 BS200P
GTIN	4061792226050
Item class	03D

Description**Version:**

Double grinding machine for grinding, sharpening, deburring and, if using a steel wire brush, also removing rust on steel and metals. The integrated LED light optimally illuminates the working area. Durable discs and very smooth running thanks to the high-quality mounting flanges.

- **Workpiece rests can be adjusted without tools.**

The universal combo bench grinder with sanding belt and grinding wheel is ideal for processing wood and metal.

- **Large belt sanding arm can be continuously tilted by 90° for two common grinding belt lengths.**
- **Tool-free pitch adjustment of the belt sanding arm.**
- **Extraction connection on the belt sanding arm, suitable for standard coupling bushes.**
- **Suitable for the use of round steel wire brushes for removing rust.**
- **Integrated LED light to optimally illuminate the work area.**
- **Flexible working on the large sanding area or alternatively on the curve of the belt sanding arm.**
- **Extraction connection on the belt sanding arm, suitable for standard coupling bushes.**
- **Rubberised drive wheel in the belt sanding arm with grooves for fast heat dissipation.**
- **Fast, tool-free sanding belt change after opening the cover.**
- **Maximum smooth running and long tool life of the discs thanks to high-quality mounting flanges.**

Supplied with:

Includes standard aluminium oxide grinding wheel 60 N, fabric sanding belt K 60, spark protection glass, workpiece rest and hexagon key.

Note:

Suitable grinding wheels can be found under No. 596100 and No. 568733.

Technical description

Power consumption	600 W
Weight	16.9 kg
Manufacturer's designation	BS 200 Plus
Power supply	Mains-powered
maximum speed	2980 min ⁻¹
Cable length	1.8 m
Linishing belt length	1000 mm
Linishing belt length	1020 mm
Linishing belt width	50 mm
Abrasive disc Ø D	200 mm
Abrasive disc hole Ø H	32 mm
Abrasive disc width T	25 mm
Rated power	230 V
Type of product	Linishing machine