



## Combination hammer, Hammer head Ø: 35mm



### Order data

Order number	754890 35
GTIN	4016134010309
Item class	73V

### Description

#### Version:

Combined **engineer's hammer and soft hammer**, sides additionally with ground striking faces for working in confined spaces. Head made of highly tempered steel with an exchangeable set of inserts made of wear-resistant nylon – shore hardness approx. 68D. With unbreakable "Ultratec" glass fibre handle.

#### Spare part:

Nylon insert No. 754895.

### Technical description

Material of the handle	Glass fibre
Overall length	324 mm
Head length with inserts	114 mm
Series	Ultratec DUO
Hammer head dimensions	34x34 mm
Weight	0.66 kg
Material of body	Heat treatable steel, induction hardened
Material of insert	Nylon, white, hard (single-ended)
Hammer head Ø	35 mm
dead-blow	no

Type of product

Hammer

---

**Accessories**

Spare insert, nylon Hammer head Ø 35 mm

754895 35