



## Combination hammer, Hammer head Ø: 40mm



### Order data

Order number	754890 40
GTIN	4016134010316
Item class	73V

### Description

#### Version:

Combined **engineer's hammer and soft hammer**, sides additionally with ground striking faces for working in confined spaces. Head made of highly tempered steel with an exchangeable set of inserts made of wear-resistant nylon – shore hardness approx. 68D. With unbreakable "Ultratec" glass fibre handle.

#### Spare part:

Nylon insert No. 754895.

### Technical description

Hammer head dimensions	38x38 mm
Material of the handle	Glass fibre
Head length with inserts	124 mm
Series	Ultratec DUO
Weight	1 kg
Material of insert	Nylon, white, hard (single-ended)
Material of body	Heat treatable steel, induction hardened
Overall length	357 mm
Hammer head Ø	40 mm
dead-blow	no

Type of product

Hammer

---

**Accessories**

Spare insert, nylon Hammer head Ø 40 mm

754895 40