



## Ultrasonic cleaning unit Elmasonic Select, Type: 18



### Order data

Order number	082000 18
GTIN	4250004100558
Item class	04S

### Description

#### Version:

For removal of oil, grease, grinding fluids, polishing fluids, paint residues, flux, oxide layers, carbon deposits, scale from nearly all surfaces and even from inaccessible places, whilst treating the component being cleaned with the utmost care. Use special power cleaner depending on the dirt and effectiveness required. The component to be cleaned must be completely surrounded by cleaning fluid.

The ultrasonic cleaning devices from the Elmasonic Select series are powerful and individual.

- **5 ultrasonic modes.**
- **4 individual cleaning programs can be saved.**
- **Clear display showing all relevant cleaning parameters.**
- **Acoustic and visual feedback about the operating status.**
- **Tray made of drawn stainless steel**

#### Supplied with:

Without component basket.

#### Note:

Further sizes and types on request. The suitable component basket can be found under No. 082101 (Elmasonic Select), No. 081204 (Elmasonic xtra TT) and No. 081203 (Elmasonic xtra ST). Ultrasonic cleaning agent and anti-corrosion agent can be found under 088015 – 088019.

### Technical description

Manufacturer's designation	Select 180
Maximum ultrasonic power	800 W
Item width	360 mm
Cleaning bath height	195 mm
Item length	405 mm
Nominal voltage	220 - 240 V
Width of component basket	250 mm
Length of component basket	280 mm
Weight	10.2 kg
Heating power	800 W
Power supply	Mains-powered
Volume	17.8 l
Recommended working volume	14.2 l
Type of product	Ultrasonic cleaning unit

---

## Accessories

Component basketSelect 18	082101 18
---------------------------	-----------