



## Ultrasonic cleaning unit Elmasonic Select, Type: 90



### Order data

Order number	082000 90
GTIN	4250004100589
Item class	04S

### Description

#### Version:

For removal of oil, grease, grinding fluids, polishing fluids, paint residues, flux, oxide layers, carbon deposits, scale from nearly all surfaces and even from inaccessible places, whilst treating the component being cleaned with the utmost care. Use special power cleaner depending on the dirt and effectiveness required. The component to be cleaned must be completely surrounded by cleaning fluid.

The ultrasonic cleaning devices from the Elmasonic Select series are powerful and individual.

- **5 ultrasonic modes.**
- **4 individual cleaning programs can be saved.**
- **Clear display showing all relevant cleaning parameters.**
- **Acoustic and visual feedback about the operating status.**
- **Tray made of drawn stainless steel**

#### Supplied with:

Without component basket.

#### Note:

Further sizes and types on request. The suitable component basket can be found under No. 082101 (Elmasonic Select), No. 081204 (Elmasonic xtra TT) and No. 081203 (Elmasonic xtra ST). Ultrasonic cleaning agent and anti-corrosion agent can be found under 088015 – 088019.

### Technical description

Width of component basket	460 mm
Item length	875 mm
Item width	595 mm
Weight	43.4 kg
Heating power	2000 W
Maximum ultrasonic power	3840 W
Nominal voltage	220 - 240 V
Length of component basket	545 mm
Cleaning bath height	285 mm
Power supply	Mains-powered
Manufacturer's designation	Select 900
Volume	89 l
Recommended working volume	63.7 l
Type of product	Ultrasonic cleaning unit

---

## Accessories

Component basketSelect 90	082101 90
---------------------------	-----------