



Ultrasonic cleaning unit Elmasonic xtra TT, Type: 6



Order data

Order number	082001 6
GTIN	4250004100299
Item class	04S

Description

Version:

For removal of oil, grease, grinding fluids, polishing fluids, paint residues, flux, oxide layers, carbon deposits, scale from nearly all surfaces and even from inaccessible places, whilst treating the component being cleaned with the utmost care. Use special power cleaner depending on the dirt and effectiveness required. The component to be cleaned must be completely surrounded by cleaning fluid.

Powerful ultrasonic cleaning by the Elmasonic xtra TT series for heavy-duty applications.

- **Greater ultrasonic effect due to selectable dynamic function.**
- **Integrated sweep function for uniform sound distribution in the cleaning bath.**
- **Visual limit temperature warning to protect sensitive parts.**
- **Individual timer and temperature control.**
- **Clearly arranged, splash-proof control panel.**

Supplied with:

Without component basket.

Note:

Further sizes and types on request. The suitable component basket can be found under No. 082101 (Elmasonic Select), No. 081204 (Elmasonic xtra TT) and No. 081203 (Elmasonic xtra ST). Ultrasonic cleaning agents and anti-corrosion agents can be found under 088015 – 088019.

Technical description

Nominal voltage	220 - 240 V
-----------------	-------------

Width of component basket	132 mm
Item length	420 mm
Manufacturer's designation	xtra TT 60H
Power supply	Mains-powered
Item width	250 mm
Length of component basket	257 mm
Weight	10 kg
Maximum ultrasonic power	400 W
Heating power	150 W
Cleaning bath height	150 mm
Volume	6.5 l
Recommended working volume	5 l
Type of product	Ultrasonic cleaning unit

Accessories

Component basketxtra TT 6	082104 6
---------------------------	----------