



## Ultrasonic cleaning unit Elmasonic xtra TT, Type: 12



### Order data

Order number	082001 12
GTIN	4250004100305
Item class	04S

### Description

#### Version:

For removal of oil, grease, grinding fluids, polishing fluids, paint residues, flux, oxide layers, carbon deposits, scale from nearly all surfaces and even from inaccessible places, whilst treating the component being cleaned with the utmost care. Use special power cleaner depending on the dirt and effectiveness required. The component to be cleaned must be completely surrounded by cleaning fluid.

Powerful ultrasonic cleaning by the Elmasonic xtra TT series for heavy-duty applications.

- **Greater ultrasonic effect due to selectable dynamic function.**
- **Integrated sweep function for uniform sound distribution in the cleaning bath.**
- **Visual limit temperature warning to protect sensitive parts.**
- **Individual timer and temperature control.**
- **Clearly arranged, splash-proof control panel.**

#### Supplied with:

Without component basket.

#### Note:

Further sizes and types on request. The suitable component basket can be found under No. 082101 (Elmasonic Select), No. 081204 (Elmasonic xtra TT) and No. 081203 (Elmasonic xtra ST). Ultrasonic cleaning agents and anti-corrosion agents can be found under 088015 – 088019.

### Technical description

Manufacturer's designation	xtra TT 120H
Weight	11 kg
Length of component basket	262 mm
Item length	440 mm
Item width	340 mm
Heating power	200 W
Nominal voltage	220 - 240 V
Cleaning bath height	200 mm
Width of component basket	222 mm
Maximum ultrasonic power	800 W
Power supply	Mains-powered
Volume	14 l
Recommended working volume	10 l
Type of product	Ultrasonic cleaning unit

---

## Accessories

Component basketxtra TT 12	082104 12
----------------------------	-----------