



Ultrasonic cleaning unit Elmasonic xtra ST, Type: 60



Order data

Order number	082002 60
GTIN	4250004100343
Item class	04S

Description

Version:

For removal of oil, grease, grinding fluids, polishing fluids, paint residues, flux, oxide layers, carbon deposits, scale from nearly all surfaces and even from inaccessible places, whilst treating the component being cleaned with the utmost care. Use special power cleaner depending on the dirt and effectiveness required. The component to be cleaned must be completely surrounded by cleaning fluid.

Elmasonic xtra ST is the ultrasonic device for the most severe dirt and is particularly suitable for extremely demanding applications in the field of industrial cleaning.

- **2 selectable ultrasonic frequencies (25 kHz for the most stubborn dirt and 45 kHz for gentle cleaning).**
- **Integrated sweep function for even sound distribution in the cleaning bath.**
- **Selectable pulse function increases the ultrasonic peak power.**
- **Dynamic function (ultrasonic power can be increased temporarily by up to 20%).**
- **Sturdy tray made from welded stainless steel.**

Supplied with:

Without component basket.

Note:

Further sizes and types on request. The suitable component basket can be found under No. 082101 (Elmasonic Select), No. 081204 (Elmasonic xtra TT) and No. 081203 (Elmasonic xtra ST). Ultrasonic cleaning agents and anti-corrosion agents can be found under 088015 – 088019.

See 082105 for suitable sound-absorption lid. Other accessories available on request.

Technical description

Cleaning bath height	330 mm
Item length	825 mm
Nominal voltage	400 V
Item width	595 mm
Power supply	Mains-powered
Length of component basket	415 mm
Width of component basket	255 mm
Manufacturer's designation	xtra ST 600H
Heating power	1400 W
Weight	55 kg
Maximum ultrasonic power	3600 W
Volume	56.3 l
Recommended working volume	45 l
Type of product	Ultrasonic cleaning unit

Accessories

Noise protection coverxtra ST 60	082105 60
Component basketxtra ST 60	082103 60