



## Ultrasonic cleaning unit Elmasonic Easy, Type: 1



### Order data

Order number	082003 1
GTIN	4250004100626
Item class	04S

### Description

#### Version:

For removal of oil, grease, grinding fluids, polishing fluids, paint residues, flux, oxide layers, carbon deposits, scale from nearly all surfaces and even from inaccessible places, whilst treating the component being cleaned with the utmost care. Use special power cleaner depending on the dirt and effectiveness required. The component to be cleaned must be completely surrounded by cleaning fluid.

The ultrasonic cleaning devices from the Elmasonic Easy series are powerful and ideal for beginners.

- **2 ultrasonic modes.**
- **Temperature can be adjusted in steps of 5°C.**
- **Electronic selector switch and LED display of all operating statuses.**
- **Acoustic and visual feedback about the operating status.**
- **Tray made of drawn stainless steel.**

#### Function:

IP20: Protected against penetration by foreign bodies with  $\varnothing < 12$  mm, however touching should be avoided, and offers no protection against water.

#### Supplied with:

Without component basket.

#### Note:

Further sizes and types on request. You can find the suitable basket under No. 082101 (Elmasonic Select, Elmasonic Xtra and Elmasonic Easy sizes 3 – 30), No. 082102 size 1 (Elmasonic Easy) and

No. 082103 (Elmasonic xtra ST). Ultrasonic cleaning agent and anti-corrosion agent can be found under No. 088015 – No. 088019.

### Technical description

Item length	235 mm
Power consumption	30 W
Item height	200 mm
Cleaning bath height	55 mm
Volume	0.9 l
Weight	2 kg
Recommended working volume	0.7 l
Power supply	Mains-powered
Width of component basket	70 mm
Heating power	60 W
Manufacturer's designation	Elmasonic Easy 1L
Capacity of cleaning bath	1 l
Length of component basket	155 mm
Cleaning bath length	185 mm
Item width	135 mm
Cleaning bath width	80 mm
IP Index of Protection	IP 20
Nominal voltage	220 - 240 V
Type of product	Ultrasonic cleaning unit