



Pliers wrench Joker 6004, self-adjusting, insulated to VDE, Type: M



Order data

Order number	813750 M
GTIN	4013288221780
Item class	63F

Description

Version:

- **Parallel guided, smooth jaws.**
- **New stepless self-adjustment by easy seating on hex-head bolts and hexagon nuts.**
- **Quick and secure screw fastening without removing the socket insert, due to the mechanical ratchet function.**
- **Lever mechanism when gripping avoids slippage and damage.**
- **Particularly small backswing angle of only 30° due to the Vee profiles in the head across the corners.**

Individually tested tool in accordance with **DIN EN IEC 60900 / VDE 0682-201**. Safety is increased by the anti-slip protection at the front end of the handle. Additional protection through the sliding function for contactless and safe opening of the non-insulated jaws.

Material:

Chrome molybdenum steel, matt chrome-plated.

Technical description

overall length	190 mm
Jaw capacity	13 - 16 mm
Manufacturer's designation	6004 Joker M
Jaw capacity	1/2 – 5/8 in
Material	Chromium-molybdenum steel
Surface	matt chrome-plated
Type of product	Pliers wrench

