



Fibre disc Actirox AF 890 (CER), Ø 115 mm, Grit: 60

Order data

Order number	566442 60
GTIN	4018875585375
Item class	56V

Description
Version:

Tear-resistant but very flexible **vulcanised fibre**. Bore diameter 22.23 mm and crossed slots. Top type VSM Actrirox AF 890 fibre discs **with very high and aggressive grinding performance**. Cool grinding and outstanding tool life.

Grit type: **100% geometrically shaped VSM ceramic grit** with abrasive coating (TOP SIZE).

Application:

Limited to maximum 80 m/s circumferential speed with backing pads No. 566650 / 6670 on angle grinders. For **grinding flat and curved surfaces** with a high degree of **flexibility**.

Technical description

Disc Ø	115 mm
Grit	60
Series	Actirox
Grinding media	Ceramic ZA Oxide mixed grit with cooling, active coating (TOP SIZE)
Grinding medium code	Ceramic

Grinding media backing	Vulcanised fibre
Iron, sulphur and chlorine constituents	< 0.1 %
Product name attribute	Ø 115 mm
Bore Ø	22.23 mm
optimised for material	Aluminium
optimised for material	INOX
maximum circumferential speed	80 m/s
Type of product	Fibre disc

User data

	Suitability	V _c	ISO code
Alu Mg	suitable		
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
INOX	suitable		
Ti	suitable		
GG(G)	suitable		
CuZn	suitable		
dry	suitable		