

**uvex****Safety helmet uvex pronamic alpine MIPS, Colour: ORANGE****Order data**

Order number	097839 ORANGE
GTIN	4031101959962
Item class	04U

**Description****Version:**

This **multi-function helmet** combines the requirements of an industrial safety helmet with the properties of a scaffolder's helmet. Pronamic stands for optimum protection (**protection**) and dynamism (**dynamic**). Comfortable width adjustment via rubberised rotary wheel. Gradual adjustment of the interior fitting for optimum fit. Generously designed ventilation openings on the side of the helmet. Comprehensive mounting elements for helmet accessories, such as face protection, safety glasses and head lamp. Lightweight and hard-wearing safety helmet of ABS. Cold-resistant **down to -30°C**.

- **4-point strap attachment**
- **30 mm Euro slot mounting**
- **PU sweatband**
- **Reaches well down on to the neck**
- **With rotary catch**

With **integrated MIPS technology**.

**Application:**

Maintenance, scaffolding, maintenance technology, assembly, work and rescues at heights.

**Standard:**

DIN EN 392; DIN EN 12492

## Technical description

Width adjustment	Rotary closure
Manufacturer's designation	pronamic alpine MIPS hi-viz orange
Colour	orange
Size	53 - 63 cm
Weight	490 g
Helmet characteristics	Beskyttelsesegenskab indtil -30 °C
Helmet characteristics	Protection against liquid metal spraying out
Helmet characteristics	Protection against lateral deformation
Material of helmet shell	ABS
Standard	DIN EN 397
Standard	DIN EN 12492
Type of product	Safety helmet