

uvex

Safety helmet uvex pronomic alpine, Colour: ORANGE



Order data

Order number	097837 ORANGE
GTIN	4031101959900
Item class	04U

Description

Version:

This **multi-function helmet** combines the requirements of an industrial safety helmet with the properties of a scaffolder's helmet. Pronamic stands for optimum protection (**pro**tection) and dynamism (**dynamic**). Comfortable width adjustment via rubberised rotary wheel. Gradual adjustment of the interior fitting for optimum fit. Generously designed ventilation openings on the side of the helmet. Comprehensive mounting elements for helmet accessories, such as face protection, safety glasses and head lamp. Lightweight and hard-wearing safety helmet of ABS. Cold-resistant **down to -30°C**.

- **4-point strap attachment**
- **30 mm Euro slot mounting**
- **PU sweatband**
- **Reaches well down on to the neck**
- **With rotary catch**

Application:

Maintenance, scaffolding, maintenance technology, assembly, work and rescues at heights.

Standard:

DIN EN 392; DIN EN 12492

Technical description

Colour	orange
Size	53 - 63 cm
Width adjustment	Rotary closure
Weight	490 g
Manufacturer's designation	pronamic alpine hi-viz orange
Helmet characteristics	Beskyttelsesegenskab indtil -30 °C
Helmet characteristics	Protection against liquid metal spraying out
Helmet characteristics	Protection against lateral deformation
Material of helmet shell	ABS
Standard	DIN EN 397
Standard	DIN EN 12492
Type of product	Safety helmet