

**metabo****Cordless hammer drill with LiHD rechargeable battery KHLTXBL24****Order data**

Order number	075560 KHLTXBL24
GTIN	4061792218529
Item class	03D

**Description****Version:****Power packs for hammer drilling.**

The hammer drill has a high-performance hammer action with a precise pneumatic impact mechanism that generates impacts with maximum impact energy with minimal pressure.

Combination hammer drill with 3 functions: **hammer drilling, drilling and chiselling.**

- **Metabo VibraTech (MVT): health-friendly, low-fatigue working even in continuous use.**
- **Vario-Tacho-Constamatic (VTC) full-wave electronics for working with material-appropriate speeds that remain constant under load.**
- **Safety shut-off: mechanical decoupling of the drive when the drill is blocked for safe working.**
- **Very light, compact cordless hammer with brushless motor for low-fatigue drilling in any working position.**
- **Maximum drilling performance, efficiency and service life thanks to brushless technology and high-performance impact mechanism.**
- **Dust-free drilling with external dust extraction ESA plus.**
- **Electronic soft start for precise spot drilling.**
- **LED work light provides a clear view of the bore area.**

**Advantage:**

**Batteries are 100% compatible – now also across different manufacturers.**

All 18 V devices and battery packs from CAS partners are 100% compatible with each other. CAS stands for "Cordless Alliance System".

**Supplied with:**

Includes 2× batteries, charger and MetaBOX.  
With additional handle and depth stop.

**Note:**

See No. 073870 – 073890 for suitable batteries and chargers.

## Technical description

Power supply	Mains operated
Tool arbor shape	SDS Plus
Manufacturer's designation	KH 18 LTX BL 24
Number of rechargeable batteries contained	2
Type of rechargeable battery	Lithium-ion
Battery voltage	18 V
Impact energy	2.2 J
maximum twist drill size Ø in steel	13 mm
maximum twist drill size Ø in concrete	24 mm
Weight without battery	2.7 kg
maximum twist drill size Ø in wood	30 mm
Battery capacity	4 Ah
Packaging	Metabox
maximum hammer rate	4750 min <sup>-1</sup>
suitable battery - supplier / battery type / voltage	Type CAS 18 V
No load speed	0 - 1280 min <sup>-1</sup>
Type of product	Hammer drill